


# WHAT IS DIFFERENCE IN LED VIEWBOX?

SUPERIOR LUMINANCE  
BEYOND LED BACK LIGHT TECHNOLOGY  
HIGH END RADIOGRAPHY VIEWER

BRILLANCE FOR YOUR X-RAY FILM

## "J" company from China

### 1) Package




Plastic & Thin Metal Case  
Poor Package

## LED Lumivision series




Aluminum Frame & Metal Case  
Professional Cushion Package

### 2) Housing Constructior



Hard to open the case to repair  
Poor Construction Structure




East to open and repair  
Organized Construction Structure

### 3) Power Supplier



External Power Adaptor at inside  
Poor Construction to built-in




Switching Mode Power Supplier (SMPS) Inverter  
Separate Dimming Control Board by On/Off Switch


## "J" company from China

## LED Lumivision series

### 4) Light Distribution




Poor Uniformity  
No Light Guide Panel at the center



Full Light Distribution (over 90% uniformity)  
Light Guide Panel at the center

### 5) Film Activation Switch (Auto Switch)



Micro Switch, built-in at the metal frame

### 6) Input Power and Cable Assy



Direct In-Put AC Power



**Point A Technologies, Inc.**

20957 Currier Road, Unit C, Walnut, CA 91746

Tel : 909-869-8949 Fax : 909-869-8959 [www.pointatech.com](http://www.pointatech.com)